



**Product #:** 5320372

**Order Symbol:** UL PC 2828 18 G

**Description:** Enclosure, PC, Opaque Screw Cover

Dimensions	Length	Width	Height
Inch	7.1	10.9	10.9
mm	180	278	278

**Materials**

Material:	Polycarbonate
Base color:	RAL 7035 -light grey
Cover color:	RAL 7035 -light grey
Gasket material:	Polyurethane

**Temperatures**

Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175
Temperature °C (short term):	-40 ... 140
Temperature °C (continuous):	-40 ... 80

**Ratings**

Ingress Protection (EN 60529):	IP66; IP67
Impact Resistance (EN 62262):	IK08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	No
UV resistance:	UL 508
Flammability Rating:	UL94-5VA (f1)/ Cover: UL94-V0 (f1)
Glow Wire Test (IEC 60695):	960 °C
UL/cUL Type:	Type 1, 3, 3S, 4, 4X, 6, 6P or 12