

by Schneider Electric

STW-6600WA Basic Web Terminal



 Aluminum Front Pane 16 Million Colors Enhanced Cybersecul 	Single Touch Analog Display
Performance Sp	ecifications
Model	STW6600WA
Graphics Display Resolu- tion	WXGA TFT (1,280 x 800 Pixels)
Display Type and Size	TFT Color LCD (12.1-inch) Wide
Display Colors	16 million colors
Touch Panel	Resistive film (analog, single touch)
Effective Display Area	261.12 x 163.2 mm (10.28 x 6.43 in)
ToucPanel Resolution	1024 x 1024
Backlight	Backlight White LED (Not user replaceable. When replacement is required contact customer support.)
Backlight Service Life	50,000 hours or more (continuous operation at 25 °C [77 °F] before by brightness decreases to 25%)
Brightness Control	16 levels (Adjusted with touch panel or software)

		Backlight		Backlight White LED (Not user replaceable. When replacement is required, contact customer support.)
		Backlight Service Life		50,000 hours or more (continuous operation at 25 °C [77 °F] before backlight brightness decreases to 25%)
	Brightness Control		16 levels (Adjusted with touch panel or software)	
	Interface	USB (Type A)	Connector: USB 2.0 (Type A) x 1, Power supply voltage: 5 Vdc ±5 %, Maxi- mum current supplied: 500 mA, Communication distance: 5 m [16.4 ft.]	
			USB (Type - microB)	The USB (micro-B) interface is disabled.
			Ethernet	IEEE802.3i/IEEE802.3u, 10BASE-T/100BASE-TX, Connector: Modular jack (RJ-45) x 2 *1

1 ETH1 and ETH2 have the same IP address and MAC address.

Features:

General Specificati	ons		
Model	STW6600WA		
Input Voltage	Rated Input Voltage: 24 Vdc / Input Voltage Limits: 19.2 to 28.8 Vdc		
Power Consumption	15 W or less when power is not supplied to devices via fron USB, 5.9 W or less when screen turns off the backlight (standby mode) (Max 18.4 W)		
In-Rush Current	30 A or less		
Storage Temperature	-20 to 60 °C (-4 to 140 °F)		
Shock Resistance	IEC/EN 61131-2 compliant 147 m/s2, X, Y, Z directions for 3 times		
Certifications	UL 61010-2-201 and CSA C22.2 No61010-2-201, KC KN1, KN61000-6-2, RCM EN61000-6-4, CE EN 61131-2, EN61000-6-4, EN61000-6-2, RoHS, REACH Regulation EC 1907/2006, WEEE Directive 2012/19/EU		
OperatingTemperature	0 to 50 °C (32 to 122 °F)		
Voltage Drop	10 ms or less		
Corrosive Gas	Free of corrosive gases		
Pollution Degree	For use in pollution degree 2 environment		
Cooling method	Natural air circulation		
Dust	0.1 mg/m3 (10-7 oz/ft3) or less (non-conductive levels)		
Voltage Endurance	1,000 Vac, 20 mA for 1 minute (between charging and FG terminals)		
Vibration Resistance	IEC/EN 61131-2 compliant, 5 to 9 Hz single amplitude 3.5 mm [0.14 in.], 9 to 150 Hz fixed acceleration: 9.8 m/s2, X, Y, Z directions for 10 cycles (approx. 100 min.)		
Insulation Resistance	500 Vdc, 10 MΩ or more		
Structure	IP65F, Type 1, Type 4X (indoor use only), Type 13 (on the front panel when properly installed in an enclosure) *2		
Weight	1.8 kg (3.97 lb) or less		
External Dimensions	313 x 235 x 50 mm (12.32 x 9.25 x 1.97 in)		
Panel Cut-Out Dimensions	295 x 217 mm (11.61 x 8.54 in) ^{*2} Panel thickness area: 1.65 mm (0.060.2 in) ^{*3}		
Warranty	Two (2) years		


2 For dimensional tolerance, everything +1/-0 mm (+0.04/-0 in) and R in angle are below R3 (R0.12 in)

3 Even if the installation wall thickness is within the recommended range for the "Panel Cut Dimensions", depending on wall's material, size, and installation location of this product and other


©2019 Pro-face. All rights reserved. Specifications may change without notice.

Pro-face[™]

by Schneider Electric



Panel Cut-Out Dimensions



Datasheet

Ordering Information			
Model Number	Description		
PFXSTW6600WAD	12.1"W Basic Web Terminal 12.1"W 1280 x 800 pixel 16M colors display with analog signal touch panel, Ethernet(RJ45) x 2, USB Host, 24VDC, non- expandable		

Options		
Part Number	Description	
PFXZCIAFTF1	Installation fastener (2 pieces/set).	
PFXZCIWG123	Installation Gasket	
CA5-DCCNM-01	Connector to connect DC power supply cables.	
PFXZCDDS122	Disposable, dirt-resistant sheet for the display (5 sheets/set) for STW-6600WA.	
FP-US00	Connects a USB device.	
CA5-USBEXT-01	Extension cable that attaches USB interface to front panel.	
PFXZCBCLUSA1	Clamp to prevent disconnection of USB cable (USB Type A, 1 port, 5 clamps/set)	

Pro-face America

Phone: 734.477.0600 www.profaceamerica.com

Customer Service Hotline: 800.289.9266

— For more information —

ACCESS www.profaceamerica.com