

## FEATURES

- Coloured Flexible magnetic roll
- Easy clean Dry-wipe vinyl finish
- Cuts to length with scissors
- Widths from 20mm to 90mm
- 10m long reel lengths
- Up to 28g/cm<sup>2</sup> pull force rating

## RS PRO Racking Strip & Bay Markers

RS Stock No.: 2655633, 2655634,

2655628, 2655631

2655632, 2655627

2655629




RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- *Our Racking Strip & Bay Markers magnetic tapes have a dry-wipe surface to let you colour code and label all your mild steel racking to make identifying all your products a fast and simple process.*
- *With 3 possible colours (Yellow, Red and White) and 5 possible widths (20mm, 30mm, 50mm, 70mm and 90mm) we have a range of options that will suit your application. Simply cut the 10metre roll with scissors to your required length.*
- *The Racking Strip & Bay Markers magnetic tapes use 0.5mm thick magnetic rubber rated at up to 28g/cm<sup>2</sup> (0.398lb/in<sup>2</sup>) of area and have a dry-wipe finish vinyl top layer (approximately 0.1mm thick). The magnetic rubber layer is magnetised multiple pole on the visible magnetic face and is slit from larger width rolls.*
- *The Racking Strip & Bay Markers magnetic tapes is easily cut to length - simply cut it with scissors (a craft knife will also work fine). It will attract to any ferrous surface, such as mild steel racking and bays, mild steel filing cabinets, fridge doors, magnetic notice boards, mild steel tape, etc.*
- *The dry-wipe vinyl layer lets you use a dry-wipe marker pen to write on and then wipe-off later. So the Racking Strip & Bay Markers magnetic tapes can be re-used as required. If you want the label to be permanent, you could use a permanent marker pen (but noting that it would not be wiped away at all easily if you did this).*

## General Specifications

<b>Magnet material type</b>	Isotropic Strontium Ferrite in a binder
<b>Magnetic Application</b>	Racking Strip & Bay Markers
<b>Temperature Range</b>	-40°C to +60°C (-40°F to +140°F)
<b>Vinyl layer</b>	PVC 
<b>Vinyl Colour</b>	Varies – see Similar Products list below
<b>Vinyl Finish</b>	Dry-wipe finish
<b>Width</b>	Varies – see Similar Products list below
<b>Length of Reel</b>	10m
<b>Thickness</b>	0.5mm
<b>Magnetic Poles Layout</b>	Multiple across width
<b>Specific Magnetic Polarity Type</b>	N/A
<b>Magnetic Pull Force rating</b>	up to 28g/cm <sup>2</sup>
<b>Method to cut to length</b>	Cut to required length using scissors or craft knife

## Similar Products

Stock No.	Brand	Vinyl Colour	Width	Length	Pull force rating	Weight	Units per pack
2655633	RS PRO	White	20mm	10m	up to 28g/cm <sup>2</sup>	0.429kg	1
2655634	RS PRO	White	30mm	10m	up to 28g/cm <sup>2</sup>	0.629kg	1
2655628	RS PRO	White	50mm	10m	up to 28g/cm <sup>2</sup>	0.917kg	1
2655631	RS PRO	White	70mm	10m	up to 28g/cm <sup>2</sup>	1.462kg	1
2655632	RS PRO	White	90mm	10m	up to 28g/cm <sup>2</sup>	1.737kg	1
2655627	RS PRO	Red	50mm	10m	up to 28g/cm <sup>2</sup>	0.917kg	1
2655629	RS PRO	Yellow	50mm	10m	up to 28g/cm <sup>2</sup>	0.917kg	1