

# MCX-PLUG RG174 RG316 CRIMP

SC9415

## SPECIFICATIONS

### ELECTRICAL:


FREQUENCY: 0-6 GHZ  
 VSWR 1.25:1 MAX  
 IMPEDANCE: 50 OHMS  
 OP. TEMP RANGE: -55C to +125C

### MECHANICAL:

MATERIAL BODY: BRASS AU PLATING 3μ"  
 CENTER CONTACT: Brass  
 CONTACT PLATING: Au MIL-G-45204  
 INSULATOR: TEFLON

### ASSEMBLY

TRIM CABLE AS SHOWN,  
 SLIDE CRIMP SLEEVE ON CABLE,  
 SOLDER ON CONTACT,  
 INSERT CABLE INTO BODY,  
 CRIMP




.192" DIA

←.27"→

←.69" OAL→

←.095"→



←.175"→

←.260"→

STRIPPING DIMENSIONS

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**MCX-PLUG RG174 RG316 CRIMP**

SIZE	CAGE CODE	DWG NO	REV
<b>A</b>	<b>3FKR5</b>	<b>SC9415</b>	
SCALE	SHEET		