

Product data sheet

Characteristics

8965RO10V01

Contacteur, 8965RO, hoist, reversing, 3HP at 480VAC, 3 phase, 24VAC coil, quick connect terminals. open style



Main

Product or Component Type	Reversing Hoist Contactor
Maximum Horse Power Rating	1 Hp 115 V AC, 1 phase 1.5 Hp 230 V AC, 1 phase 3 Hp 230 V AC, 3 phase 3 Hp 460 V AC, 3 phase 3 hp 575 V AC, 3 phase

Complementary

Product Certifications	UL Listed CSA
Poles description	3P
[Uc] control circuit voltage	24 V AC 60 Hz
Phase	3 phase
Range of Product	RO

Ordering and shipping details

Category	21406-8965 R - REVERSING HOIST CONTACTORS
Discount Schedule	CP1
GTIN	785901032175
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.50 in (8.9 cm)
Package 1 Width	4.88 in (12.4 cm)
Package 1 Length	6.61 in (16.8 cm)
Package 1 Weight	28.80 oz (816.5 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Under investigation
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------