



Main

Range	I-Line
Product or Component Type	Interiors
Circuit Breaker Type	B-Frame J-frame H-frame Q-Frame QO
Enclosure Type	Distribution enclosure

Complementary

Main Type	Main lugs
Width	26.44 in (671.58 mm)
Height	48.02 in (1219.71 mm)
Depth	8.7 in (220.98 mm)
Localization on Device	Interior
Product Destination	Enclosure HCJ 32 in (812.80 mm) 73 in (1854.20 mm) 9.5 in (241.30 mm)
Rated Current	400 A
Number of Phases	3 phase
Mounting Space	63 in (1600.20 mm)
Bus Material	Aluminium busbar
Enclosure Material	Painted steel
Tightening torque	251.98 lbf.in (28.47 N.m) 0.02...0.23 in ² (13.3...151 mm ²) (AWG 6...300 kcmil)

Environment

Standards	cULus
-----------	-------

Ordering and shipping details

Category	00016-I-LINE PB RTA
Discount Schedule	PE1A
GTIN	785901237204
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.25 in (23.495 cm)
Package 1 Width	31.00 in (78.74 cm)
Package 1 Length	49.00 in (124.46 cm)
Package 1 Weight	87.00 lb(US) (39.463 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile