



Main

Product name	PowerPacT
Product or Component Type	Trip unit
Trip unit rating	225 A
Trip unit technology	Thermal-magnetic
Circuit breaker type	J-frame

Complementary

Number of poles	3
[Ue] rated operational voltage	600 V AC
[Ics] rated service short-circuit breaking capacity	80 %
Tightening torque	7.97...9.74 Lbf.in (0.9...1.1 N.m) 43.37...46.91 lbf.in (4.9...5.3 N.m)

Environment

Product Certifications	UL CSA
------------------------	-----------




Ordering and shipping details

Category	01103-H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	785901483731
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.90 in (9.906 cm)
Package 1 Width	3.70 in (9.398 cm)
Package 1 Length	4.60 in (11.684 cm)
Package 1 Weight	15.84 oz (449.056 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------