



## Main

Product range	8501N
Product type	Relay Socket
Pin shape	Spade
Number of pins	5
[In] rated current	15 A 300 V AC

## Complementary

Electrical connection	Double tiered screw clamp terminals
Mounting type	DIN rail Panel
Package quantity	1

## Environment

Certifications	UL Recognized CSA CE
Height	2.87 in (73.02 mm)
Width	0.79 in (20.06 mm)
Depth	1.14 in (28.95 mm)

## Ordering and shipping details

Category	21142-8501 N
Discount Schedule	CP2
GTIN	785901137276
Returnability	Yes
Country of origin	TW

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	1.20 in (3.048 cm)
Package 1 Length	4.10 in (10.414 cm)
Package 1 Weight	1.28 oz (36.287 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	200
Package 2 Height	13.70 in (34.798 cm)
Package 2 Width	9.20 in (23.368 cm)
Package 2 Length	10.20 in (25.908 cm)
Package 2 Weight	16.50 lb(US) (7.484 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------