



## Main

|              |     |
|--------------|-----|
| Product line | QO  |
| Product type | Bar |

## Complementary

|                           |  |
|---------------------------|--|
| Number of connectors      | 9  |
| Wire size                 | AWG 14...AWG 10 copper<br>AWG 12...AWG 10 aluminium<br>AWG 8 aluminium/copper<br>AWG 6...AWG 4 aluminium/copper<br>AWG 14...AWG 12 |
| Provided equipment        | 2 screw  |
| Bar length                | 3.78 in (96 mm)  |
| Maximum length of segment | 3.15 in (80 mm)  |
| Device mounting           | Direct mounting back of enclosure  |
| Height                    | 0.437 in (11.10 mm)  |
| Depth                     | 0.312 in (7.92 mm)   |
| Tightening torque         | 20 lb.in, AWG 14...AWG 10, copper<br>20 lb.in, AWG 12...AWG 10, aluminium<br>35 lb.in, AWG 6...AWG 4                               |

## Ordering and shipping details

|                   |                         |
|-------------------|-------------------------|
| Category          | 00102-QO LC ACCESSORIES |
| Discount Schedule | DE3A                    |
| GTIN              | 785901026396            |
| Returnability     | Yes                     |
| Country of origin | US                      |

## Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 0.30 in (0.76 cm)    |
| Package 1 Width              | 0.70 in (1.78 cm)    |
| Package 1 Length             | 3.80 in (9.65 cm)    |
| Package 1 Weight             | 1.76 oz (49.9 g)     |
| Unit Type of Package 2       | PAL                  |
| Number of Units in Package 2 | 2160                 |
| Package 2 Height             | 26.80 in (68.072 cm) |
| Package 2 Width              | 40.00 in (101.6 cm)  |

|                  |                            |
|------------------|----------------------------|
| Package 2 Length | 48.00 in (121.92 cm)       |
| Package 2 Weight | 314.00 lb(US) (142.428 kg) |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| California proposition 65  | WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| REACH free of SVHC         | Yes  |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>             |
| Toxic heavy metal free     | Yes  |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>   |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>  |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|