



Main

Range Compatibility	PacDrive 3
Product or Component Type	Servo motor
Device short name	SH3.....P

Complementary

Maximum mechanical speed	6000 rpm
[Us] rated supply voltage	115...480 V
Phase	Three phase
Continuous stall current	4.8 A
Continuous stall torque	51.33 lbf.in (5.8 N.m) 115...480 V three phase
Continuous power	1900 W
Peak stall torque	161.97 lbf.in (18.3 N.m) 115...480 V three phase
Nominal output power	580 W 115 V single phase 1090 W 230 V single phase 1930 W 400 V three phase 2210 W 480 V three phase
Nominal torque	48.68 Lbf.in (5.5 N.m) 115 V single phase 46.02 Lbf.in (5.2 N.m) 230 V single phase 40.71 Lbf.in (4.6 N.m) 400 V three phase 38.94 lbf.in (4.4 N.m) 480 V three phase
Nominal speed	1000 rpm 115 V single phase 2000 rpm 230 V single phase 4000 rpm 400 V three phase 4800 rpm 480 V three phase
Maximum current Irms	17.1 A
Shaft end	Parallel key
Shaft diameter	0.75 in (19 mm)
Shaft length	1.57 in (40 mm)
Key width	0.24 in (6 mm)
IP degree of protection	Shaft bushing without shaft seal ring IP54 EN/IEC 60034-5 Motor IP65 EN/IEC 60034-5 Shaft bushing IP65 EN/IEC 60034-5
Encoder type	Absolute single turn SinCos Hiperface
Speed feedback resolution	128 periods
Holding brake	Without
Mounting Support	International standard flange
Motor flange size	3.94 in (100 mm)
Electrical Connection	Rotatable right angled connector
Torque constant	1.21 N.m/A 248 °F (120 °C)
Back emf constant	77 V/krpm 68 °F (20 °C)
Number of motor poles	4

Rotor inertia	2.31 kg.cm ²
Stator resistance	2.4 Ohm
Stator inductance	19.5 mH
Maximum radial force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm
Maximum axial force Fa	160 N
Type of cooling	Natural convection
Length	8.05 in (204.5 mm)
Centring collar diameter	3.74 in (95 mm)
Centring collar depth	0.14 in (3.5 mm)
Number of mounting holes	4
Mounting holes diameter	0.35 in (9.0 mm)
Circle diameter of the mounting holes	4.53 in (115 mm)
Product Weight	12.79 lb(US) (5.8 kg)

Ordering and shipping details

Category	18359-PACDRIVE3 SERVO MOTORS
Discount Schedule	PC52
GTIN	3606485296753
Returnability	No
Country of origin	DE

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.81 in (30.0 cm)
Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	14.55 lb(US) (6.6 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------