

Product data sheet

Characteristics

9422RS1

Disconnect mechanism, circuit breaker, variable depth, 600A, 3 pole, operator only, for PowerPacT D and L breakers



Main

Range	9422R
Product	Circuit Breaker Mechanism
Mounting Type	Flange rod variable depth
Certifications	CSA UL Recognized
Circuit Breaker Type	MG-NSJ 3 PowerPacT D 3
Handle Type	Ordered separately

Ordering and shipping details

Category	21732-9422
Discount Schedule	CP1
GTIN	785901551430
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.80 in (17.272 cm)
Package 1 Width	12.30 in (31.242 cm)
Package 1 Length	13.30 in (33.782 cm)
Package 1 Weight	7.34 lb(US) (3.329 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------