



Main

Product or Component Type	Straight length
Range of Product	I-Line

Complementary

Line Rated Current	600 A
Short Circuit Rating	22 kA
Busbar Material	Aluminium busbar
Integral Ground	50 percent capacity integral ground bus
Rated Voltage	600 V AC
Number of Phases	3 phase
Wiring configuration	3-wire
Length	10 ft (3.05 m)

Ordering and shipping details

Category	20318-AP W/GRD 600A 3WIRE-INDL
Discount Schedule	PE8
GTIN	785901653264
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.98 in (15.2 cm)
Package 1 Width	4.76 in (12.1 cm)
Package 1 Length	120.51 in (306.1 cm)
Package 1 Weight	96.00 lb(US) (43.545 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------