



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2EU
Product or Component Type	Switch-disconnector-fuse
Poles description	3P
Protected poles description	3t
Contacts type and composition	3 NO
[I _{th}] conventional free air thermal current	30 A 104 °F (40 °C)
[I _e] rated operational current	30 A
Fuse type	UL
Fuse size	J
Network type	DC AC
Network Frequency	50/60 Hz

Complementary

Type of operating handle	External frontal
Mounting Support	Rail Plate
[U _i] rated insulation voltage	750 V
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	15 KW 400 V 18.5 KW 500 V 25 kW 690 V
Short-circuit withstand	17.6 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles
Connections - terminals	Power circuit lugs-ring terminals 0.00...0.02 in ² (2...13 mm ²)
Tightening torque	Power circuit 58.41 lbf.in (6.6 N.m)

Environment

Standards	UL98 CSA C22.2 No 4
IP degree of protection	IP20 IEC 60529 with terminal cover)
Ambient Air Temperature for Operation	-4...158 °F (-20...70 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)
Fire resistance	1760 °F (960 °C) body
Height	5.35 in (136 mm)
Width	5.88 in (149.3 mm)
Depth	4.84 in (123 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22640-IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	3606480618529
Returnability	Yes
Country of origin	TN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.38 in (16.2 cm)
Package 1 Width	6.81 in (17.3 cm)
Package 1 Length	7.09 in (18.0 cm)
Package 1 Weight	4.63 lb(US) (2.1 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information