

# Product data sheet

## Characteristics

# PDC6HD6

Circuit breaker accessory, PowerPacT H, power distribution connectors, 15A to 150A, qty 3



### Main

Circuit breaker type	Standard
Quantity per Set	Set of 3
AWG gauge	AWG 14...AWG 6 copper
Product destination	HD/HG/HJ/HL circuit breaker 15...100 A

### Complementary

Tightening torque	327.48 Lbf.in (37 N.m) 0.04...0.08 in <sup>2</sup> (25...50 mm <sup>2</sup> ) (AWG 8...AWG 6) 20.36 lbf.in (2.3 N.m) 0.00...0.01 in <sup>2</sup> (2.5...6 mm <sup>2</sup> ) (AWG 14...AWG 10)
-------------------	--

### Ordering and shipping details

Category	01103-H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	785901470991
Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.60 in (1.524 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	4.30 in (10.922 cm)
Package 1 Weight	5.28 oz (149.686 g)

### Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------