



## Main

Product or Component Type	Miniature circuit-breaker
Range of Product	QOU
Circuit breaker type	Standard
Circuit breaker application	HACR rated

## Complementary

Line Rated Current	15 A
Electrical connection	Slotted box lugs, line side Slotted box lugs, load side
[Ue] rated operational voltage	120/240 V AC 120 V AC 48 V DC
Mounting Mode	Unit mount
AWG gauge	AWG 14...AWG 2 aluminium/copper
Height	4.05 in (102.87 mm)
Width	1.5 in (38.10 mm)
Depth	2.95 in (74.93 mm)
Tightening torque	45 lbf.in (5.08 N.m) (AWG 14...AWG 2)

## Environment

Product Certifications	UL Listed CSA IEC
------------------------	-------------------------

## Ordering and shipping details

Category	00900-QOU BREAKERS & SWITCH
Discount Schedule	DE2
GTIN	785901418658
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	4.90 in (12.446 cm)
Package 1 Weight	5.93 oz (168.0 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	1008

Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	777.00 lb(US) (352.441 kg)
Unit Type of Package 3	CAR
Number of Units in Package 3	24
Package 3 Height	3.70 in (9.398 cm)
Package 3 Width	13.60 in (34.544 cm)
Package 3 Length	20.70 in (52.578 cm)
Package 3 Weight	18.74 lb(US) (8.5 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------