

Product data sheet

Characteristics

9422ATDF631

Operating mechanism, flange mounted, variable depth, 60A, 600 V, fuseholder, switch mechanism, 6 inch handle, NEMA 4



Main

Range	9422T
Product	Disconnect Switch
Disconnect Type	Fusible disconnect switch

Complementary

Mounting Type	Flange rod variable depth
Current Rating	60 A
Horsepower Rating	15 Hp 200 V AC 15 Hp 230 V AC 30 Hp 460 V AC 50 Hp 575 V AC 10 hp 250 V DC
Fuse Rating	60 A 600 V
Handle Type	6 in handle included NEMA 1/3/3R/4 enclosures sheet steel
Fuse Type	J R H K

Environment

Certifications	UL Recognized CSA
----------------	----------------------

Ordering and shipping details

Category	21732-9422
Discount Schedule	CP1
GTIN	785901872191
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.10 in (18.034 cm)
Package 1 Width	11.20 in (28.448 cm)
Package 1 Length	16.00 in (40.64 cm)
Package 1 Weight	9.05 lb(US) (4.105 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------