



## Main

Product	Double Throw Safety Switch
Duty Rating	General duty
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	None
Number of Poles	4
Current Rating	400 A
Voltage Rating	600 V AC 600 V DC
Enclosure Rating	NEMA 1
Motor power hp	125 Hp at 240 V AC 50-60 Hz for 3 phase motors 250 Hp at 480 V AC 50-60 Hz for 3 phase motors 350 Hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 250 V DC

## Complementary

Short-circuit current	10 KA H or K 100 kA R, J or T
Fuse type	H or K R, J or T
Mounting Type	Surface
Wire Size	AWG 1/0...750 kcmil aluminium/copper
Tightening torque	550 Lbf.in (62.14 N.m) 0.08...0.47 in <sup>2</sup> (53.49...304 mm <sup>2</sup> ) (AWG 1/0...750 kcmil) 62.14 lbf.in (7.02 N.m) 0.08...0.24 in <sup>2</sup> (53.49...152 mm <sup>2</sup> ) (2 x AWG 1/0...2 x 300 kcmil)
Depth	8.88 in (225.55 mm)
Width	28.40 in (721.36 mm)
Height	64.20 in (1630.68 mm)
Product Weight	220.46 lb(US) (100 kg)

## Environment

Certifications	UL Listed
----------------	-----------

## Ordering and shipping details

Category	00033-DT SWITCH,NEMA1
Discount Schedule	DE1
GTIN	3606481716798
Returnability	No
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.00 in (43.18 cm)
Package 1 Width	36.00 in (91.44 cm)
Package 1 Length	66.00 in (167.64 cm)
Package 1 Weight	248.00 lb(US) (112.49 kg)

## Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

EU RoHS Directive

Under investigation

Environmental Disclosure

 [Product Environmental Profile](#)