

Product data sheet

Characteristics

GS2AH140

External rotary handle, TeSys GS, red handle, front mounting, 2 positions I-O, NEMA 3R, for GS 30 to 400A UL



Main

Range of Product	TeSys
Range	TeSys
Device short name	GS2AH
Product or Component Type	Rotary handle
Range compatibility	TeSys (TeSys GS) GS2EU TeSys (TeSys GS) GS2GU TeSys (TeSys GS) GS2JU TeSys (TeSys GS) GS2MU TeSys (TeSys GS) GS2QU
Type of operating handle	External frontal
Handle colour	Red
Handle front plate colour	Yellow

Complementary

Handle positions	O-I
Rotary handle padlocking	With
Switch rated current	30 A 60 A 100 A 200 A 400 A
Standards	CSA UL
Product Weight	0.53 lb(US) (0.24 kg)

Environment

NEMA Degree of Protection	NEMA 3R/12
---------------------------	------------

Ordering and shipping details

Category	22640-IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	3389119411844
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	4.72 in (12.0 cm)
Package 1 Length	6.30 in (16.0 cm)
Package 1 Weight	8.71 oz (247.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	15
Package 2 Height	11.81 in (30.0 cm)

Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	9.15 lb(US) (4.15 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------