



Main

Product Range	Type S
Component type	Auxiliary Contact Module
Used with	Contactors starter

Complementary

NEMA size	0 3 6 7 4 5 1 00 2
Auxiliary contact composition	1 NO
[Uc] control circuit voltage	<= 600 V AC 50/60 Hz
Rated breaking capacity	6 A 120 V AC inductive control circuit UL 508 3 A 240 V AC inductive control circuit UL 508 1.2 A 600 V AC inductive control circuit UL 508 1.5 A 480 V AC inductive control circuit UL 508 10 A <= 600 V AC resistive control circuit UL 508
Height	1.5 in (38.10 mm)
Width	3 in (76.20 mm)
Depth	4.5 in (114.30 mm)
Product Weight	0.20 lb(US) (0.09 kg)

Environment

Product Certifications	CSA UL Listed UL Recognized
------------------------	-----------------------------------

Ordering and shipping details

Category	21761-9999 DISCOUNT CP1
Discount Schedule	CP1
GTIN	785901733300
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	3.10 in (7.874 cm)
Package 1 Length	4.60 in (11.684 cm)
Package 1 Weight	3.20 oz (90.719 g)
Unit Type of Package 2	PAL
Number of Units in Package 2	21
Package 2 Height	8.00 in (20.32 cm)
Package 2 Width	11.30 in (28.702 cm)
Package 2 Length	14.20 in (36.068 cm)
Package 2 Weight	12.40 lb(US) (5.625 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------