



Main

Product	Surge protection device
Range	Surgelogic

Complementary

Voltage Rating	208Y/120 V AC
MCOV	180 V
SCCR	200 kA
Surge Current	40 kA
Nominal Discharge Current	10 kA
Number of Phases	3 phase
Wiring Configuration	4-wire
Connection	Wire AWG 12 copper
Local Signalling	Status LED normal operation
Cable length	24 in (609.60 mm)
Mounting Support	Panel mounting
Height	3.07 in (78 mm)
Width	3.62 in (92 mm)
Depth	2.64 in (67 mm)

Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 4X
Enclosure Material	Black Plastic
Standards	UL 1449:ed. 4 CSA C22.2 No 8:1986

Ordering and shipping details

Category	08462-SURGE PROTECTION SDSA
Discount Schedule	DE1B
GTIN	785901602569
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.50 in (8.89 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	5.00 in (12.7 cm)
Package 1 Weight	15.68 oz (444.521 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	6.00 in (15.24 cm)
Package 2 Width	16.50 in (41.91 cm)
Package 2 Length	17.00 in (43.18 cm)
Package 2 Weight	20.74 lb(US) (9.407 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes