



## Main

Product	Miniature circuit-breaker
Range	QO
Current Rating	125 A
Voltage Rating	120/240 V AC 240 V AC 120 V AC
Mounting Type	Bolt-on
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Box lugs

## Complementary

Interrupt Rating	22 KA 120/240 V AC 50/60 Hz 22 KA 240 V AC 50/60 Hz 22 kA 120 V AC 50/60 Hz
Number of Panel Spaces	6
Wire Size	AWG 4...300 kcmil copper or aluminium
Tightening Torque	40.71 lbf.in (4.6 N.m)
Height	5.71 in (145 mm)
Width	4.49 in (114 mm)
Depth	4.88 in (124 mm)
Product Weight	0.96 lb(US) (0.435 kg)

## Environment

Certifications	UL Listed CSA
Ambient Rating	104 °F (40 °C)

## Ordering and shipping details

Category	00015-QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	785901065470
Returnability	Yes
Country of origin	MX

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.30 in (10.922 cm)
Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	6.80 in (17.272 cm)
Package 1 Weight	3.95 lb(US) (1.792 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	558
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)

Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	2216.00 lb(US) (1005.16 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Cadmium and cadmium compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------