

9001SKR8P1RH25

Illuminated push-button, Harmony 9001SK, plastic, mushroom 41mm, red, 30mm, 3 positions, return to center, 110-120V, 1 NC late + 1 NC



Main

| | |
|---------------------------------|-------------------------|
| Range of Product | Harmony 9001SK |
| Product or Component Type | Illuminated push-button |
| Device short name | 9001SK |
| Operator additional information | Screw-on plastic |

Complementary

| | |
|-------------------------------|---|
| Bezel material | Plastic |
| Mounting diameter | 1.18 in (30 mm) |
| Contacts type and composition | 1 NC late break + 1 NC |
| Contact operation | Late-break |
| Mechanical durability | 5000000 cycles |
| Device presentation | Complete product |
| Cap/operator or lens colour | Red |
| [Us] rated supply voltage | 110...120 V |
| Light block supply | Via integral transformer |
| Operator profile | Mushroom Ø 41 mm |
| Type of operator | Pull : spring return, center : stay put, push : spring return |
| Operator position information | 3 positions |
| Supply frequency | 50...60 Hz |
| Size | 30 mm |
| Bulb base | BA 9s |
| Light source | Incandescent bulb |

Environment

| | |
|---------------------------|--|
| Standards | EN/IEC 60947-5-1 UL 508 EN/IEC 60947-5-4 JIS C 4520 EN/IEC 60947-1 JIS C 852 CSA C22.2 No 14 |
| IP degree of protection | IP66 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13 |

Ordering and shipping details

| | |
|-------------------|-------------------|
| Category | 21429-9001 SK,SKY |
| Discount Schedule | CS1 |
| GTIN | 785901042990 |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 6.35 in (16.129 cm) |
| Package 1 Width | 2.50 in (6.35 cm) |
| Package 1 Length | 16.13 in (40.968 cm) |
| Package 1 Weight | 8.64 oz (244.94 g) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|