



Main

Range	MD
Product	Motor Disconnect Switch
Current Rating	60 A
Horsepower Rating	20 Hp 220/240 V AC 40 Hp 440/480 V AC 40 hp 600 V AC
Enclosure Rating	NEMA 4X
Certifications	UL Listed

Complementary

Height	8.27 in (210.06 mm)
Width	4.94 in (125.48 mm)
Depth	4.37 in (111.00 mm)
Product Weight	2.12 lb(US) (0.96 kg)

Ordering and shipping details

Category	21734-TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	3606480190230
Returnability	Yes
Country of origin	TN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.80 in (12.2 cm)
Package 1 Width	5.51 in (14.0 cm)
Package 1 Length	10.04 in (25.5 cm)
Package 1 Weight	33.47 oz (949.0 g)
Unit Type of Package 2	S04
Number of Units in Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	27.87 lb(US) (12.64 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	48
Package 3 Height	30.31 in (77.0 cm)
Package 3 Width	31.50 in (80.0 cm)
Package 3 Length	23.62 in (60.0 cm)
Package 3 Weight	130.21 lb(US) (59.06 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Formaldehyde (gas), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

