



Main

Range of Product	Harmony 9001K
Product or Component Type	Illuminated push-button
Device short name	K
Operator additional information	Screw-on plastic

Complementary

Bezel material	Metal
Mounting diameter	1.18 in (30 mm)
Light source	Incandescent bulb
Bulb base	BA 9s
Light block supply	Without supply
Contacts type and composition	1 C/O
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product
Cap/operator or lens colour	Red
[Us] rated supply voltage	110...120 V
Light block supply	Via integral transformer
Operator profile	Mushroom Ø 41 mm
Type of operator	Push-pull
Operator position information	2 positions
Supply frequency	50...60 Hz
Size	30 mm

Environment

Product Certifications	CSA LR 25490 class 3211 03 UL listed file E42259 CCN NKCR NEMA CE
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	785901034179
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.35 in (16.129 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	16.13 in (40.968 cm)
Package 1 Weight	9.28 oz (263.084 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------