



### Main

Product or Component Type	Communication card
Range Compatibility	Altivar 71 Altivar 61Q Altivar 61 Altivar 71Q
Communication Port Protocol	Profibus DP
Connector Type	9-way female SUB-D connector
Transmission Rate	1.5 Mbps 12 Mbps 9600 bps 3 Mbps 500 kbps 19.2 kbps 187.5 kbps 6 Mbps 93.75 kbps

### Complementary

Number of addresses	1...126
Communication service	CiA 402 profile I/O profile I/O data Communication monitoring can be inhibited, adjustable PPO type 5
Display type	1 LED DX (data exchange) 1 LED ST (status) Graphic display terminal control word received Graphic display terminal I/O data Graphic display terminal reference received
Product Weight	0.66 lb(US) (0.3 kg)

### Ordering and shipping details

Category	22135-ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	3389118067165
Returnability	Yes
Country of origin	ID

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.83 in (7.200 cm)
Package 1 Width	6.69 in (17.000 cm)
Package 1 Length	9.06 in (23.000 cm)
Package 1 Weight	9.91 oz (281.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)

Package 2 Weight	5.54 lb(US) (2.512 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	56
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	66.99 lb(US) (30.388 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

### Contractual warranty

Warranty	18 months
----------	-----------