



M-12694


5




TYPICAL 15A DEVICE





TYPICAL 20A DEVICE



TYPICAL BLANK FACE DEVICE




TYPICAL 20A DEVICE BLANK FACE SWITCH 1.5 HP SHOWN AT 180° TO VIEW FACE TEXT



BACK MARKINGS TYPICAL

(RANDOM UNIT CONFIGURATION SHOWN. SEE BOM FOR UNIT DETAIL AND VARIATIONS)

| LIST OF PARTS | | |
|-----------------|------------|--------|
| DESCRIPTION | MATERIAL | FINISH |
| FACE | ZYTEL 101F | |
| BRIDGE | STEEL | |
| CONTACTS | BRASS | |
| CLAMP PLATES | BRASS | |
| BASE | ZYTEL 101F | |
| MOUNTING SCREWS | STEEL | |
| BINDING SCREWS | STEEL | |



| REV | DESCRIPTION | APP | DATE |
|-----|---|-----|------------|
| 5 | ADDED ISO VIEW TO DRAWING PER DCN 23357 | TFB | 09-25-2017 |
| 4 | ADDED GFCI BLANK FACE SWITCH 1.5 HP VIEW AND CATALOG NUMBERS FOR THIS DEVICE TO TABLE CHART PER DCN 21621 | TFB | 06-30-2016 |
| 3 | REDRAWN IN INVENTOR. ADDED BLANK FACE VIEW PER DCN 21981 | DJR | 03-09-2016 |
| 2 | UPDATED MATERIALS PER DCN 21241 | KP | 05-25-15 |
| 1 | INITIAL RELEASE PER DCN 20675 | TFH | 9-02-2014 |

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
CUSTOMER DWG. GFCI COMM. ST NON-TR / TR / BF



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED
.XX = ±.01
.XXX = ±.005
ANGLE TOL. ±2°

DR. BY DJR
CHK. BY KP

SCALE 1:1
DATE 9-02-14

GFCI COMMERCIAL SELF TEST STANDARD NON-TR / TR / BF

| CONFIGURATION | BROWN | IVORY | WHITE | GRAY | BLACK | RED | ALMOND | LT. ALMOND | RATING |
|-------------------|----------|-----------|-----------|------------|------------|-----------|------------|------------|-----------|
| 15A TR | GFTRST15 | GFTRST15I | GFTRST15W | GFTRST15GY | GFTRST15BK | GFTRST15R | GFTRST15AL | GFTRST15LA | 15A, 125V |
| 20A TR | GFTRST20 | GFTRST20I | GFTRST20W | GFTRST20GY | GFTRST20BK | GFTRST20R | GFTRST20AL | GFTRST20LA | 20A, 125V |
| 15A NON-TR | GFRST15 | GFRST15I | GFRST15W | GFRST15GY | GFRST15BK | GFRST15R | GFRST15AL | GFRST15LA | 15A, 125V |
| 20A NON-TR | GFRST20 | GFRST20I | GFRST20W | GFRST20GY | GFRST20BK | GFRST20R | GFRST20AL | GFRST20LA | 20A, 125V |
| BLANK FACE | GFBFST20 | GFBFST20I | GFBFST20W | GFBFST20GY | GFBFST20BK | GFBFST20R | GFBFST20AL | GFBFST20LA | 20A, 125V |
| BLANK FACE 1.5 HP | GFBFHP20 | GFBFHP20I | GFBFHP20W | GFBFHP20GY | GFBFHP20BK | GFBFHP20R | GFBFHP20AL | GFBFHP20LA | 20A, 125V |