



Datasheet

RS PRO NiCd battery 3.6v 150mah for TSX

Manufacturer Part Number: 2321105

EN



General Specifications

| | |
|------------------------------|---|
| Technology | Ni-CD |
| Type | 1/3 AA |
| Designation | 3S1P |
| Nominal Voltage | 3.6v |
| Nominal Capacity | 0.15ah |
| Max Charge Voltage | 5.1V |
| Standard charge | 15 mA |
| Fast Charge | 150mA |
| Operating Voltage | 2.7v to 4.2v |
| Operating Temperature | Charge 0 to 35°C Discharge -30 to 60°C |
| Storage Temperature | -30 to 35°C |
| Cycle Life at 80% DOD | ~500 |



| | |
|--|----------|
| Internal Resistance (At 1000HZ) | < 210 mΩ |
| Shelf Life | 2 Years |
| Charge frequency during storage | 6 months |

Mechanical Specifications

| | |
|-------------------------|--------------------------------|
| Dimensions (MM) | 50.5 x 14 (+/-1) |
| Weight (G) | 24 gr (+/-1) |
| Covering | Shrink Sleeve |
| Output Connector | Cosses CI 1 Picot Saft 10/14mm |

Approvals

| | |
|-------------------------------|---------|
| Certification | None |
| Battery Energy | 0.54 WH |
| Transport Restrictions | None |

rspro.com