

# EZM3800GCBA30

EZ Meter Main, Center Tap, 800A 65 kAIC  
Breaker, 3000A I-Line II, Aluminum, 3P



## Main

Range of Product	EZ meter-pak
Product or Component Type	Meter centre busway centre tap main unit
Main type	Main Circuit Breaker
Included Items	Circuit-breaker 1) 3P 800 A 65 kA main supply, ready assembled

## Complementary

Main rated current	800 A
Bus rated current	3000 A
Material	Aluminium busbar
Enclosure Material	Steel
[Ue] rated operational voltage	208Y/120 V AC 240/120 V delta AC
Device mounting	Wall mounted
Number of Phases	3 phase in 3 phase out
Service feed location	OH
Electrical connection	I-Line connection
Wiring configuration	4-wire
Height	43.07 in (1093.98 mm)
Width	22.72 in (577.09 mm)
Depth	14.76 in (374.90 mm)

## Environment

Product Certifications	UL Listed
Enclosure Rating	NEMA 3R

## Ordering and shipping details

Category	00020-EZ METER-PAK
Discount Schedule	DE4
Nbr. of units in pkg.	1
Package weight(Lbs)	595.20 lb(US) (269.978 kg)
Returnability	No

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	43.07 in (109.4 cm)
Package 1 width	22.72 in (57.7 cm)
Package 1 Length	14.76 in (37.5 cm)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>