

FEATURES

- Floor mount
- Multistage temperature control with up to 3 heating stages
- Integrated room thermostat
- Overheat protection
- Fan moto with thermal protection
- Condensation free heating, no oxygen consumption
- Portable and easy to use
- Thermostat control type
- Plug is type C - European plug
- Power settings are 2
- Airflow of 386m³/ h
- Water resistant

3kW Fan Heater, Floor Mounted, Type C - European Plug

RS Stock No.: 174-6570



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO fan heater is a portable, small and a practical source of heat. It has a high-quality stainless steel heating element and adjustable thermostat control. Also, this fan provides overheat protection with time delay. The insulated handle is for safer carrying. It is enabled with a built-in high-temperature resistant silicone wire. The heater operates on a supply voltage of 220V-240V and outputs a maximum power of 3kW. It has a heating area of 30m².

General Specifications

Heat Type	Fan
Air Flow	386m ³ /h
Control Type	Thermostat
Power Settings	2
Heating Area	30m ²
Applications	Automobile workshop, Construction area, Assembly operation, Food and beverage, Storeroom and workshop, Greenhouse

Electrical Specifications

Input Power Rating	220-240v ~50hz
Maximum Output Power	3kW
Voltage Rating	230V ac
Plug Type	Type C - European Plug

Mechanical Specifications

Mounting	Floor Mounted
-----------------	---------------

Protection Category

IP Rating

IPX4

Approvals

Compliance/Certifications

IPX4 rated, ANSI/ESD S20.20:2014, BS EN 61340-5-1:2007



