

RS PRO Energy efficient Panel Heater



with integral 7 day 24 hour LCD electronic timer and controls
 Stock No: 1962386,1962388



The 24/7 Panel Heater connects directly to the permanent electricity supply offering two heat output settings depending on your heating needs. The timer option allows user to select one of 12 pre-set programmes or create a customised 'DIY' heating programme. Wall fixtures are included.

Key Features

- Silent in operation
- Lot 20 compliant
- High efficiency of airflow with over 95% of used energy creating heat
- User friendly LCD display screen
- 12 pre-set programmes available
- 1 user defined programme available
- Program and real-time clock memory function
- Thermostat for temperature setting (5°C-30°C)
- Adjustable temperature in Normal and Economic modes
- 24 hour On/Off Timer
- Anti-frosting function
- Ionizer function
- Child safety lock
- Over-heat safety protection
- IP24 rated

Technical Specifications

| Model | 494823 | 494824 | 494825 |
|-----------------------|-------------------------|-------------------------|-------------------------|
| Power | 1000W | 1500W | 2000W |
| Colour | White | White | White |
| Heating setting | 1000W | 1500W | 2000W |
| Heating area | 10-13m ² | 15-18m ² | 20-23m ² |
| Voltage | 230-240V (50Hz) | 230-240V (50Hz) | 230-240V (50Hz) |
| Approval | CE, EMC, LVD, RoHS, ERP | CE, EMC, LVD, RoHS, ERP | CE, EMC, LVD, RoHS, ERP |
| Product size (HxWxD) | 440 x 455 x 125mm | 440 x 615 x 125mm | 440 x 775 x 125mm |
| Packaged size (HxWxD) | 505 x 520 x 155mm | 505 x 680 x 155mm | 505 x 840 x 155mm |
| Heater weight | 4kg | 5.1kg | 6.5kg |
| Gross weight | 5.1kg | 6.3kg | 7.9kg |