

Datasheet

Type A Male Adaptor x BSPP Female End



Image representative of range

Technical Specifications:

Specifications	
Gasket	Buna-N Nitrile
Temperature Rating	-40° C to +100° C

Features & Benefits:

- **Manufactured to interchange with all products produced to MIL-C-27487F**
- **BSP male threads to BS21 (Taper)**
- **BSP female threads to BS2779 (Parallel)**

Pressure Ratings:

- **Recommendations based on the use of mating fittings at ambient temperature 20°C with standard Nitrile seals installed.**

RS Article	Size	Material	Working Pressure
362-6649	1"	Aluminium	17.2 bar
233-3273	1"	Polypropylene	7 bar
317-490	1"	Stainless Steel	17.2 bar
233-3289	1.1/2"	Polypropylene	7 bar
317-507	1.1/2"	Stainless Steel	17.2 bar
362-6661	2"	Aluminium	17.2 bar
233-3295	2"	Polypropylene	7 bar
307-178	2"	Stainless Steel	17.2 bar