

FEATURES

- Fan heater
- Floor-mounted
- Two power settings
- Maximum output power of 2 kW
- Air flow of 197 m³/h
- Thermostat controls
- Type G British 3-pin plug
- Heating area of 20 m²
- Supply voltage of 220-240 V

2kW Fan Heater, Floor Mounted, Type G - British 3-pin

RS Stock No.: 174-6567



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This small, floor-mounted fan heater is a portable and practical source of heat. The heating element is made of stainless steel, which is a reliable and efficient conductor. Robust and energy-efficient, fan heaters such as this are commonly found in workshops and storerooms. This 2 kW fan heater doesn't produce condensation during use, so it won't cause damp, mould or mildew. It's also protected from overheating thanks to a handy time delay, which turns it off when it reaches a pre-set temperature. An adjustable thermostat controls the heat output. For safer carrying, there's a sturdy insulated handle.

General Specifications

Heat Type	Fan
Air Flow	197m ³ /h
Control Type	Thermostat
Power Settings	2
Safety Thermostat	Yes
Heating Area	20m ²
Applications	Automobile workshop, Construction area, Assembly operation, Food and beverage, Storeroom and workshop, Greenhouse

Electrical Specifications

Maximum Output Power	2kW
Voltage Rating	230V ac
Frequency	50Hz
Plug Type	Type G - British 3-pin

Mechanical Specifications

Mounting	Floor Mounted
Dimensions	217mm x 210mm x 160mm
Height	217mm
Width	210mm
Depth	160mm

Approvals

Compliance/Certifications	EN69335-1:2012+A1, EN60335-2-30:2009+A11, RoHS
----------------------------------	--



