

**Alternate Catalog No. S802U-K10**  
**Catalog No. 2CCS862017R0427**

**Description: MCB S800 2P K 10A**

**UPC No 7612271214012**

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

S802U-K10 2 Pole K Characteristic 10A 50kA 240/415VAC High Performance Circuit Breaker HPCB



Representative Image

**Descriptors**

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

**Specifications**

Number of Poles	2
Tripping Characteristic	K
Rated Current	10 A
Standards	IEC/EN 60947-2 UL 489 CSA C22.2 No.5
Product Main Type	S800U
Rated Voltage (V)	(240 V AC)
Interrupting Rating acc. to UL489	(240 V AC) 50 kA
Rated Ultimate Short-Circuit Breaking Capacity	(415 V AC) 50 kA
Power Loss	1.5 W