

Features

- Powerful Cortex A35 1.2GHz processor
- Compact dimensions, Shallow depth behind panel
- IIoT MQTT Client
- App for iOS and Android Smart Phones and Tablets
- RS232, 422/485
- Ethernet
- Micro USB port
- Comprehensive user manual & configuration software downloads on RS Website product page
- Configuration software includes 300+ popular PLC Serial Protocols

RS PRO HMI. 10.2 inch, 1024x600 Backlit TFT LCD. 16k Colours. CANopen

RS Stock No.: 2508929



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- HMI's are used to monitor machines, perform tasks and visualise operational status. The display can be programmed to display status, instructions, soft messages and SCADA systems.
Soft buttons on the touch screen reduce the requirement for separately mounted push-buttons and selector switches thus saving you component cost, installation cost and panel space.
- This large 15.0 inch model will be suited to many applications that require cloud communications for remote monitoring, control and updates, together with a greater amount of graphics and enhanced viewability.

It can also be accessed via the manufacturers iOS/Android App 'IIoT Box' which offers remote HMI screen emulation for monitoring and control on Smart Phones and Tablets

- Use HMI's to monitor and control Air Conditioning and Temperature Control systems, Access control and many types of machinery.

General Specifications

| | |
|--------------------------------|--------------------------------------|
| General: | |
| Operating System | Linux 4.4.0 QT based |
| Processor | Cortex A35 1.2GHz |
| Display | |
| Size | 15.0" |
| Resolution | 1920 x 1080 |
| Colours | 260,000 colours |
| Brightness (c/m ²) | 220 |
| Backlight | LED |
| Backlight Lifetime | 50,000 Hours |
| Touch Panel | High Precision 4-wire resistive |
| Storage: | |
| Memory | 512MB |
| Flash | 4GB |
| SD Card Slot | Yes |
| USB Port | USB 2.0 Host, USB 2.0 Client |
| RTC: | |
| Real Time Clock | No |
| Calendar | Yes |
| I/O Port, COM1 | CN1:RS422/485, CN2:RS232, CN3: RS485 |
| Ethernet | Yes |
| IIoT | MQTT Client |
| | LUA Script |

Electrical Specifications

| | |
|----------------------|------------|
| Rated Power | <15W |
| Power Voltage | 24VDC |
| Supply Voltage range | 12 - 28VDC |

Mechanical Specifications

| | |
|---------------------|------------------------------|
| Housing Colour | Silver |
| Housing Material | Aluminium + Metal + ABS |
| Max. Dimensions, mm | 403.0 x 253.0 x 35.2 (W,H,D) |
| Panel cut-out, mm | 390.0 x 244.0 (W, H) |
| Mounting method | Through panel mount |
| | VESA 75 fixings |
| Weight (Kg) | 2.46 |

Operation Environment Specifications

| | |
|-----------------------------|--|
| Operating Temperature range | -10 - +60°C |
| Storage Temperature | 0 - +50°C |
| Humidity | 10 - 90% RH (non-condensing) |
| Vibration Resistance | 10~25Hz (X, Y, Z directions 2G/30 minutes) |
| Cooling | Air cooling |

Protection Category

| | |
|-----------|--------------------|
| IP Rating | IP65 (Front Panel) |
|-----------|--------------------|

Approvals

| | |
|----------------------------|-------------------------------|
| Compliance/ Certifications | UKCA/CE/FCC Class A |
| Declarations | MFR Declaration of Conformity |

Configuration

| | |
|-----------------------------------|---|
| RS PRO HMI Editor User Manual | Download from product page on RS Components website |
| PI Studio Configuration Software | Download from product page on RS Components website |
| APP for remote monitoring/control | IIoT Box: Free from Apple App Store or download from; http://v-box.net/theme/html/app.html |

Similar Products

| Stock Number | Short Description |
|--------------|---|
| 2508924 | RS PRO Touch-Screen HMI, 3.5" TFT LCD 320 x 240. USB, RS422/485, 232 |
| 2508925 | RS PRO Touch-Screen HMI, 4.3" TFT LCD 480 x 272. USB, RS422/485, 232 |
| 221-3481 | RS PRO Touch-Screen HMI, 4.3" TFT LCD 480 x 272, Ethernet, USB, RS422/485, 232 |
| 215-6604 | RS PRO Touch-Screen HMI, 7.0" TFT LCD 800 x 480, USB, RS422/485, 232 |
| 215-6605 | RS PRO Touch-Screen HMI, 7.0" TFT LCD 800 x 480, Ethernet, USB, RS422/485, 232 |
| 2508926 | RS PRO Touch-Screen HMI, 7.0" TFT LCD 800 x 480, Ethernet, USB, RS422/485, 232, CANopen |
| 215-6607 | RS PRO Touch-Screen HMI, 7.0" TFT LCD 800 x 480, Ethernet, USB, RS422/485, 232, IIoT MQTT Client. LUA Script. Remote monitoring/update via cloud server. Remote HMI Screen emulation and operation via iOS/Android App |
| 215-6606 | RS PRO Touch-Screen HMI, 10.2" TFT LCD 1024 x 600 |
| 2508928 | RS PRO Touch-Screen HMI, 10.2" TFT LCD 800 x 480, Ethernet, USB, RS422/485, 232, IIoT MQTT Client. LUA Script. Remote monitoring/update via cloud server. Remote HMI Screen emulation and operation via iOS/Android App |
| 2508927 | RS PRO Touch-Screen HMI, 10.2" TFT LCD 800 x 480, Ethernet, USB, RS422/485, 232, CANopen |
| 2508929 | RS PRO Touch-Screen HMI, 15.0" TFT LCD 800 x 480, Ethernet, USB, RS422/485, 232, IIoT MQTT Client. LUA Script. Remote monitoring/update via cloud server. Remote HMI Screen emulation and operation via iOS/Android App |

Dimensions, mm

