



### Main

Range	ClimaSys
Product name	ClimaSys CC
Product or Component Type	Simple thermostat
Temperature setting range	32...140 °F (0...60 °C)
Information Displayed	Temperature in °C

### Complementary

Input voltage	250 V
Sensor Type	Bimetal
Contacts type and composition	NC
Contact resistance	10 mOhm
Service Life in Cycles	100000 cycles
Maximum switching capacity	2 A 120...250 V AC inductive 0.6 10 A 250 V AC resistive 15 A 120 V AC resistive 30 W DC
Electrical connection	4 terminals 2.5 mm <sup>2</sup>
Mounting Mode	Clipped
Height	External 2.68 in (68 mm)
Width	External 1.30 in (33 mm)
Depth	External 1.73 in (44 mm)
Product Weight	1.41 oz (40 g)
Mounting Location	Spacial upright 35 mm DIN rail Cross rails On mounting plate
Ambient Air Temperature for Operation	-4...176 °F (-20...80 °C)
IP Degree of Protection	IP20
Hysteresis	7 K +/- 0.4K
Number of outputs	1 heating function
Material	PC
Color	Light gray
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UL

### Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480152498
Returnability	Yes
Country of origin	DE

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	3.20 in (8.128 cm)
Package 1 Weight	2.24 oz (63.504 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------