



Main

Bereich	Spacial
Kategorie	Lifting accessory
Product or Component Type	Lifting eye
Anwendung	Multi-purpose
Mounting Location	Enclosure top
Range compatibility	Spacial (Spacial CRN) Spacial (Spacial S3D)
Device composition	2 eyebolt 2 bracket 2 washer 2 nut Fixing elements
Quantity per Set	Set of 1

Complementary

Material	Eyebolt moulded steel Bracket galvanised steel
Surface Finish	Zinc coated
Fixing mode	Screwed
Permanent permissible load	440.92 lb(US) (200 kg) slinging at 60°
Height	2.17 in (55 mm)
Width	4.72 in (120 mm)
Depth	1.18 in (30 mm)
Diameter	1.14 in (29 mm)
ISO thread	M8
Product Weight	0.53 lb(US) (0.24 kg)

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480168727
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.50 in (3.81 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	5.00 in (12.7 cm)
Package 1 Weight	0.60 lb(US) (0.27 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	8.27 in (21 cm)
Package 2 Width	15.94 in (40.5 cm)
Package 2 Length	11.81 in (30 cm)
Package 2 Weight	24.43 lb(US) (11.082 kg)
Unit Type of Package 3	P12

Number of Units in Package 3	640
Package 3 Height	17.72 in (45 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	390.90 lb(US) (177.31 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------