



Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	15.75 in (400 mm)
Nominal width	23.62 in (600 mm)
Nominal depth	7.87 in (200 mm)
Product installation	Wall-mounting
Device composition	1 body 1 lock door 1 door

Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Solid
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door stainless steel 304L Lock zamak Hinge stainless steel
Surface finish	Body and door Scotch-Brite® brushed Lock chromium plated
Product Weight	20.11 lb(US) (9.124 kg)

Environment

Standards	IEC 62208
Product Certifications	CAN/CSA 22 UL 508 type A
IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Environmental characteristic	Specific hygiene Corrosive

Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480155161
Returnability	Yes
Country of origin	BG

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.66 in (22.0 cm)
Package 1 Width	16.14 in (41.0 cm)
Package 1 Length	24.41 in (62.0 cm)
Package 1 Weight	20.11 lb(US) (9.124 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	30
Package 2 Height	78.74 in (200.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	647.06 lb(US) (293.5 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------