



Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure nominal dimensions	-
Mounting Location	Step slide Direct fixing on backstuds
Mounting plate description	Plain
Range compatibility	Spacial (Spacial S3D) Spacial (Spacial CRN) Spacial (Spacial S3X) Thalassa (Thalassa PLM)
Quantity per Set	Set of 1
Material	Fibreglass reinforced polyester
Color	Gray RAL 7035

Complementary

Fixing mode	Screwed on backstuds M8 By fixing element
Permanent permissible load	139.11 Lb(US) (63.1 kg) S3D, CRN, S3X enclosures 139.11 lb(US) (63.1 kg) PLM enclosure
Maximum load	330.69 Lb(US) (150 kg) PLM enclosure 330.69 lb(US) (150 kg) S3D, CRN, S3X enclosures
Height	Nominal 30.12 in (765 mm) Enclosure nominal dimension 31.50 in (800 mm)
Width	Nominal 21.65 in (550 mm) Enclosure nominal dimension 23.62 in (600 mm)
Surface and useful surface	4.53 ft ² (42.1 dm ²)
Thickness	0.20 in (5 mm)
Product Weight	8.38 lb(US) (3.8 kg)
Variant particularity	With enclosures H800 x W1200

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480183522
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.20 in (0.5 cm)
Package 1 Width	21.65 in (55.0 cm)
Package 1 Length	30.12 in (76.5 cm)
Package 1 Weight	8.35 lb(US) (3.787 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------