



Main

| | |
|------------------------------------|--|
| Range | Spacial |
| Accessory / separate part category | Mounting accessory |
| Product or Component Type | Mounting plate |
| Device Application | Multi-purpose |
| Enclosure nominal dimensions | - |
| Mounting Location | Step slide Direct fixing on backstuds |
| Mounting plate description | Plain |
| Range compatibility | Spacial (Spacial S3D) Spacial (Spacial CRN) Spacial (Spacial S3X) Thalassa (Thalassa PLM) |
| Quantity per Set | Set of 1 |
| Material | Fibreglass reinforced polyester |
| Color | Gray RAL 7035) |

Complementary

| | |
|----------------------------|--|
| Fixing mode | Screwed on backstuds M8 By fixing element |
| Permanent permissible load | 1929.05 lb(US) (875 kg) |
| Height | Nominal 26.18 in (665 mm) Enclosure nominal dimension 27.56 in (700 mm) |
| Width | Nominal 17.72 in (450 mm) Enclosure nominal dimension 19.69 in (500 mm) |
| Thickness | 0.16 in (4 mm) |
| Product Weight | 4.63 lb(US) (2.1 kg) |

Ordering and shipping details

| | |
|-------------------|-------------------------------------|
| Category | 80036-ENCLOSURE SYSTEMS ACCESSORIES |
| Discount Schedule | ES1 |
| GTIN | 3606480183515 |
| Returnability | No |
| Country of origin | ES |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.16 in (0.4 cm) |
| Package 1 Width | 17.72 in (45.0 cm) |
| Package 1 Length | 26.18 in (66.5 cm) |
| Package 1 Weight | 4.75 lb(US) (2.155 kg) |
| Unit Type of Package 2 | PAL |
| Number of Units in Package 2 | 100 |
| Package 2 Height | 39.37 in (100.0 cm) |
| Package 2 Width | 47.24 in (120.0 cm) |

| | |
|------------------|--------------------------|
| Package 2 Length | 39.37 in (100.0 cm) |
| Package 2 Weight | 509.27 lb(US) (231.0 kg) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|