



### Main

Range	Thalassa
Accessory / separate part category	Enclosure accessory
Product or Component Type	Door
Application	Multi-purpose
For enclosure nominal dimensions	-
Mounting Location	Front side
Range compatibility	Thalassa (Thalassa PLM)
Device composition	1 door 1 handle 4 fixing brackets

### Complementary

Material	Polyester charged with fibreglass
Color	Gray RAL 7035)
Lock type	Lock 5 mm double bar
Number of locks	2
Door type	Internal plain
Door opening side	Reversible 110 °)
Height	Grid pattern 16.34 in (415 mm)
Width	Grid pattern 12.01 in (305 mm)
Depth	Available depth between enclosure door 1.02 in (26 mm) Available depth between rear 5.98 in (152 mm)

### Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480774195
Returnability	Yes
Country of origin	ES

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.57 in (4.0 cm)
Package 1 Width	14.37 in (36.5 cm)
Package 1 Length	19.49 in (49.5 cm)
Package 1 Weight	3.84 lb(US) (1.74 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	20.08 in (51.0 cm)
Package 2 Width	11.02 in (28.0 cm)
Package 2 Length	1.97 in (5.0 cm)
Package 2 Weight	19.31 lb(US) (8.76 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>