



Main

Range	Spacial
Product name	Spacial S3DC
Application	Multi-purpose
Category	Compact enclosure
Enclosure nominal height	47.24 in (1200 mm)
Enclosure nominal width	31.50 in (800 mm)
Enclosure nominal depth	11.81 in (300 mm)
Door type	Solid
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Installation accessory type	Wall-mounting
Device composition	1 body 1 door 1 lock

Complementary

Body type	Gutter-shaped front profile double sheet thickness Single piece body
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 points lock, screw driver insert
Accessibility for operation	Front
Removable parts	Door by hinges
Material	steel
Surface finish	Epoxy-polyester powder
Color	Gray RAL 7035)
Standards	IEC 62208
Product Certifications	UL
Product Weight	98.33 lb(US) (44.6 kg)

Environment

NEMA Degree of Protection	NEMA 4X/13
IK degree of protection	IK10 IEC 62262
IP degree of protection	IP66 IEC 60529

Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480314247
Returnability	Yes
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.72 in (45.0 cm)
Package 1 Width	32.28 in (82.0 cm)
Package 1 Length	51.57 in (131.0 cm)
Package 1 Weight	98.33 lb(US) (44.6 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	3
Package 2 Height	57.09 in (145.0 cm)
Package 2 Width	33.07 in (84.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	320.55 lb(US) (145.4 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------