



### Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure nominal dimensions	-
Mounting Location	Direct fixing on backstuds Step slide
Mounting plate description	Plain
Range compatibility	Spacial (Spacial S3D) Spacial (Spacial CRN) Spacial (Spacial S3X) Thalassa (Thalassa PLM)
Quantity per Set	Set of 1
Material	Fibreglass reinforced polyester
Color	Gray RAL 7035)

### Complementary

Fixing mode	Screwed on backstuds M8 By fixing element
Permanent permissible load	110.23 lb(US) (50 kg)
Height	Nominal 18.31 in (465 mm) Enclosure nominal dimension 19.69 in (500 mm)
Width	Nominal 13.78 in (350 mm) Enclosure nominal dimension 15.75 in (400 mm)
Thickness	0.16 in (4 mm)
Product Weight	2.65 lb(US) (1.2 kg)

### Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480183492
Returnability	No
Country of origin	ES

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.16 in (0.4 cm)
Package 1 Width	13.78 in (35.0 cm)
Package 1 Length	18.31 in (46.5 cm)
Package 1 Weight	2.58 lb(US) (1.172 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------