



## Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

## Main

Range	Spacial
Accessory / separate part category	Mounting accessory
Product or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure nominal dimensions	- H: 31.50 in (800 mm) W: 23.62 in (600 mm) - H: 31.50 in (800 mm) W: 47.24 in (1200 mm)
Mounting Location	Step slide Direct fixing on backstuds
Mounting plate description	Telequick perforated
Range compatibility	Spacial (Spacial S3D) Spacial (Spacial CRN) Spacial (Spacial S3X) Thalassa (Thalassa PLM)
Quantity per Set	Set of 1
Material	steel
Surface Finish	Zinc coated

## Complementary

Fixing mode	Screwed on backstuds M8 By fixing element
Height	29.53 in (750 mm)
Width	21.69 in (551 mm)
Depth	0.59 in (15 mm)
Thickness	0.08 in (2 mm)
Product Weight	6.97 lb(US) (3.16 kg)
Number of slots	867
Variant particularity	With enclosures H800 x W1200 Installation in rear of enclosure
Cut-out dimensions	11 x 26 mm

## Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480183768
Returnability	Yes
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	21.85 in (55.5 cm)
Package 1 Length	29.72 in (75.5 cm)
Package 1 Weight	7.01 lb(US) (3.18 kg)
Unit Type of Package 2	PAM
Number of Units in Package 2	126
Package 2 Height	35.43 in (90.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	945.78 lb(US) (429.0 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------