

# NSYS3X121030

Wall mounted enclosure, Spacial S3X,  
stainless steel 304L, double plain door,  
1200x1000x300mm, IP55



## Main

Range	Spacial
Product name	Spacial S3X
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	47.24 in (1200 mm)
Nominal width	39.37 in (1000 mm)
Nominal depth	11.81 in (300 mm)
Product installation	Wall-mounting
Device composition	1 body 2 door 1 lock door 1 reinforcement frame drilled door

## Complementary

Body type	Single piece body, cross-shaped structure Gutter shaped front rail
Door type	Solid
Number of doors	Front face 2
Door opening side	Reversible 120 °)
Lock type	3 points lock, 3 mm double-bar
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Body and door stainless steel 304L Hinge stainless steel
Surface finish	Body and door Scotch-Brite® brushed
Product Weight	114.20 lb(US) (51.8 kg)

## Environment

Standards	IEC 62208
Product Certifications	CAN/CSA 22 UL 508 type A
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262
Environmental characteristic	Specific hygiene Corrosive

## Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES 1
GTIN	3606480154997
Returnability	Yes
Country of origin	BG

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	48.00 in (121.92 cm)
Package 1 Width	12.00 in (30.48 cm)
Package 1 Length	40.00 in (101.6 cm)
Package 1 Weight	75.00 lb(US) (34.02 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------