



## Main

Range	Thalassa
Product name	Thalassa PLA
Enclosure type	Multi-purpose
Product or Component Type	Suitable enclosure
Version	PLA
Nominal height	49.21 in (1250 mm)
Nominal width	49.21 in (1250 mm)
Nominal depth	16.54 in (420 mm)
Enclosure mounting	Floor-standing
Device composition	1 top part 1 bottom part 2 side part 2 door 2 rear panel

## Complementary

Body type	Sealed top and bottom part assembled with side parts
Door type	Solid front
Number of doors	2
Door opening side	Right and left 120 °)
Lock type	4 points lock, 5 mm double-bar
Accessibility for operation	Front Rear
Removable parts	Door by hinges Rear panel by fixing element
Material	Polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208 UL 508 A
NEMA Degree of Protection	NEMA 1 NEMA 12 NEMA 2 NEMA 13
Product Certifications	DNV Marine Veritas UL/cUL listed
Electrical Insulation Class	Class II

## Environment

IP degree of protection	IP65 IEC 60529 completely sealed)
IK degree of protection	IK10 IEC 62262 plain door)
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature for Storage	-31...194 °F (-35...90 °C)

## Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480774577
Returnability	No
Country of origin	ES

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	55.00 in (139.7 cm)
Package 1 Width	17.50 in (44.45 cm)
Package 1 Length	50.00 in (127 cm)
Package 1 Weight	176.00 lb(US) (79.83 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>