



Overview

Lead time	Usually Ships within 4 Weeks
-----------	------------------------------

Main

Range	ClimaSys
Product name	ClimaSys CC
Product or Component Type	Electronic hygrotherm
Temperature setting range	-40...176 °F (-40...80 °C)
Humidity setting range	20...80 %
Display Type	OLED screen
Information Displayed	Temperature in °F Relative humidity Temperature in °C

Complementary

Input voltage	90...140 V AC
Sensor Type	Optional NTC external sensor
Maximum switching capacity	4 A 120 V AC
Electrical connection	8 connectors 2.5 mm ²
Mounting Mode	By screws Clipped
Height	External 3.35 in (85 mm)
Width	External 2.20 in (56 mm)
Depth	External 1.73 in (44 mm)
Mounting Location	35 mm DIN rail Cross rails On mounting plate Spacial upright
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)
Hysteresis	2 K programmed value
Hysteresis	3 %
Number of outputs	2 ventilation/heating function
Material	PC
Color	Light gray
Flame retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UR

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	80036-ENCLOSURE SYSTEMS ACCESSORIES
Discount Schedule	ES1
GTIN	3606480152580
Returnability	No
Country of origin	ES

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.30 in (5.842 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.40 in (8.636 cm)
Package 1 Weight	5.60 oz (158.759 g)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------