

NSYPLM86VG

Wall mounted polyester enclosure,
Thalassa PLM, plain door, with handle,
847x636x300mm, IP66, IK10, RAL 7035



Main

Range	Thalassa
Product name	Thalassa PLM
Device short name	PLM
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	33.35 in (847 mm)
Nominal width	25.04 in (636 mm)
Nominal depth	11.81 in (300 mm)
Enclosure mounting	Wall mounted
Device composition	1 body 1 door 1 handle lock
Door type	Solid
Lock type	3 points lock, handle with 1242E key lock

Complementary

Number of locks	1
Mounting plate description	Without mounting plate
Accessibility for operation	Front
Removable parts	Door by hinges
Material	Polyester reinforced with fibreglass
Color	Gray RAL 7035)
Standards	IEC 62208 NEMA classification 4X NEMA classification 13
Product Certifications	UL
Electrical Insulation Class	Class II

Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK10 IEC 62262
Fire resistance	1760 °F (960 °C) IEC 62208
Ambient Air Temperature for Operation	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	80034-ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	3606480776809
Returnability	No
Country of origin	ES

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.98 in (66.0 cm)
Package 1 Width	12.99 in (33.0 cm)
Package 1 Length	34.25 in (87.0 cm)
Package 1 Weight	41.01 lb(US) (18.6 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile