

Eaton L1530PWBK

Catalog Number: L1530PWBK

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 250V, Back wiring, Black, Steel, Watertight, L15-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67

General specifications



Product Name

Eaton Arrow Hart watertight locking plug

Catalog Number

L1530PWBK

UPC

032664709012

Product Length/Depth

6.75 in

Product Height

3.75 in

Product Width

4.25 in

Product Weight

1.025 lb

Compliances

RoHS Compliant

Certifications

cULus Listed

NOM



Powering Business Worldwide

Electrical Ratings

Amperage Rating

30A

Degree of protection

IP67

NEMA configuration

L15-30

Number Of Poles

Three-pole

Number of wires

Grounding

4

Torque rating

20 lbf-inch

Voltage rating

3Ø 250 V

Environmental Specifications

Environmental resistance

IP67

NEMA 6P

NEMA 6

NEMA 4

NEMA 4X

Installation Specifications

Allowable wire size

#18-10 AWG

Wiring method

Back

Material Specifications

Color

Black

Contact material

Nickel plated brass

Product Specifications

Application

Industrial

Cord diameter

0.43-1.15 in

Design type

Watertight locking plug

Device grade

Extra heavy-duty industrial specification grade

Face/body material

Nylon

Material

Santoprene

Special features

Watertight

Resources

Brochures

[Complex environment devices brochure](#)

Multimedia

[Arrow Hart Watertight Plugs, Connectors and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - L1530PWBK](#)

Type

Locking plug



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia