

Eaton L1530PY

Catalog Number: L1530PY

Eaton severe duty locking plug, #18-10 AWG, 30A, Industrial, 250V, Back wiring, Yellow, black, Severe duty, L15-30, Three-pole, Four-wire, Thermoplastic, 0.63 to 1.16 in

General specifications



Product Name	Catalog Number
Eaton Arrow Hart severe duty locking plug	L1530PY
	UPC
	040893643519
Product Length/Depth	Product Height
4.75 in	3.75 in
Product Width	Product Weight
3.75 in	0.86 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	NOM

defaultTaxonomyAttributeLabel

Special features

Watertight locking plug

Type

Locking plug

Amperage Rating

30A

Voltage rating

3Ø 250 V

Contact material

Nickel plated brass

Application

Industrial

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back

Environmental conditions

Corrosion resistant

Number of wires

Grounding

4

Number Of Poles

Three-pole

Color

Yellow

Black

Cord diameter

0.63-1.16 in (15.9-29.4 mm)

Material

Santoprene thermoplastic elastomeric

Operating temperature

-40 to 75 °C (-40 to 167 °F)

Allowable wire size

#18-10 AWG

NEMA configuration

L15-30

Resources

Brochures

[Complex environment devices brochure](#)

Specifications and datasheets

[Eaton Specification Sheet - L1530PY](#)

Torque rating

20 lbf-inch

Design type

Safety grip

Face/body material

Nylon



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia