

# Eaton L1530P

Catalog Number: L1530P

Eaton locking plug, #16-12 AWG, 30A, Industrial, 250V, Back wiring, Black, white, Ultra grip, L15-30, Three-pole, Four-wire, Nylon



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart standard locking plug	L1530P
<b>UPC</b>	<b>Product Length/Depth</b>
032664544897	2.04 in
<b>Product Height</b>	<b>Product Width</b>
3.77 in	2.04 in
<b>Product Weight</b>	<b>Compliances</b>
0.24 lb	Federal Specifications Classification W-C375
	RoHS Compliant

## Certifications

UL Listed  
NOM  
CSA certified

## defaultTaxonomyAttributeLabel

### Special features

Severe duty locking connector

### Type

Locking plug

### Amperage Rating

30A

### Voltage rating

3Ø 250 V

### Contact material

Brass

### Application

Industrial

### Device grade

Commercial

### Wiring method

Back

### Number of wires

4

Grounding

### Number Of Poles

Three-pole

### Color

Black

White

### Cord diameter

0.25-0.69 in (6.4 mm-17.5 mm)

### Material

Thermoplastic

### Operating temperature

-20 to 60 °C (-4 to 140 °F)

### Allowable wire size

#16-12 AWG

### NEMA configuration

L15-30

### Torque rating

20 lbf-inch

## Resources

### Brochures

[Wiring Devices Buyer's Guide](#)

### Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

### Specifications and datasheets

[Eaton Specification Sheet - L1530P](#)

Design type

Standard locking plug

Face/body material

Thermoplastic



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)